

# BLAST AUTO-CLAVE

## SPECIALLY FOR CLEAN ROOMS

With all-round vision and enhanced ventilation, BLAST AUTOCLAVE provides unbeatable comfort.



BLCLAVE



103 g

- + VENTILATED FRAME AND HIGH-COMFORT**
- + AUTOCLAVABLE GOGGLES**
- + OVERFLOW CHUTE FOR LIQUIDS**
- + ADJUSTABLE STRAP AND CLEAN**
- + FITS OVER PRESCRIPTION GLASSES**
- + POLYCARBONATE LENS WITHOUT COATING**
- + COMPATIBLE WITH HALF-MASK RESPIRATOR**

**bolle**  
SAFETY

# BLAST AUTO-CLAVE

## SPECIALLY FOR CLEAN ROOMS

| MODEL                       | VERSIONS             | REFERENCES | LENS MARKING | FRAME MARKING | COATINGS |
|-----------------------------|----------------------|------------|--------------|---------------|----------|
| <b>BLAST<br/>AUTO-CLAVE</b> | Ventilated Autoclave | BLCLAVE    | ☞ 1 BT ☞     | ☞ EN166 BT ☞  | -        |

### LENS MARKING

#### Optical class symbols:

1. Continuous work

#### Mechanical strength symbols:

- B.** Medium energy impact, resists a 6 mm, 0.86 g ball at 120 m/s.
- T.** The letter T, immediately after the mechanical strength symbol, authorises use for high speed particles at extreme temperatures.

#### Others symbols:

☞ European standard ☞ Manufacturer name

### FRAME MARKING

**EN 166:** guaranteed minimum resistance of the protective eyewear against everyday risks including dropping the protective eyewear onto the ground, ageing by light exposure, exposure to heat or corrosion etc.

**B.** Medium energy impact, resists a 6 mm, 0.86 g ball at 120 m/s.

**T.** The letter T, immediately after the mechanical strength symbol, authorises use for high speed particles at extreme temperatures.

☞ European standard ☞ Manufacturer name

**Bollé Safety product approval certificates to CE standards will be sent on request.**

### CLEANING AND STORAGE

**CLEANING:** The lenses should be cleaned regularly. Bollé Safety recommends only using the B-clean lens cleaning system.

**MAINTENANCE:** Pitted, scratched or damaged lenses must be replaced by replacing the complete product. If the frame is damaged also replace the complete product. After each use it is recommended to keep the spectacles or goggles in a microfiber pouch or rigid case.

**STORAGE:** All products must be stored in a dry and clean environment.

| PACKAGING AND EAN 13 CODE        |               |
|----------------------------------|---------------|
|                                  | BLCLAVE       |
| Individual plastic bag           | 3660740000653 |
| 5 safety goggles per box         | 3660740100650 |
| 65 safety goggles per outer pack | 3660740200657 |

| CHARACTERISTICS          |                        |
|--------------------------|------------------------|
| LENSES                   | PC - 2,2 mm - Curve 5  |
| FRAME                    | Special Auto-Clave TPR |
| TEMPLES                  | Non applicable         |
| STRAP                    | Adjustable             |
| FOAM                     | No                     |
| MAINTENANCE AND CLEANING | Soapy water            |



01/10/2013

Europe Bollé Safety  
95 rue Louis Guérin  
69100 Villeurbanne - France  
Tél. : 00 33 (0) 4 78 85 23 64  
Fax : 00 33 (0) 4 78 85 28 56  
contact@bolle-safety.com

**bolle-safety.com**

U.K. Bollé Safety  
Unit C83 - Barwell Business Park Leatherhead Road - Chessington  
Surrey - KT9 2NY  
Tél. : 00 44 (0)208 391 4700  
Fax : 00 44 (0)208 391 4733  
e-mail : sales@bolle-safety.co.uk

**bolle**  
SAFETY